

SERVICE DROP GRIPS

⚠ WARNING

Cancer and Reproductive Harm: www.p65warnings.ca.gov



KEY FEATURES

- ✓ Support cables in manufacturing, industrial and open space environments
- ✓ Extended eye makes facilitates installation at connection points
- ✓ Available in Galvanised or 304 Stainless Steel wire

Use these grips to support cables in manufacturing, industrial and open space environments. The extended eye allows for easy installation and hanging from conveniently placed connection points. Also great for control room and wire to rack applications.

Slingco Part No.	Range (mm)	Range (in)	Wire Material	Wire Material	Eye Length (mm)	Eye length (in)	Approx. Break Load (kg)	Approx. Break Load (lb)
ZCS7684	5.6 - 8.1	0.22 - 0.32	Galvanised	Galvanized	229	9	499	1,100
ZCS7685	7.6 - 10.9	0.30 - 0.43	Galvanised	Galvanized	229	9	499	1,100
ZCS7686	10.4 - 14.2	0.41 - 0.56	Galvanised	Galvanized	229	9	499	1,100
ZCS7687	13.5 - 18.5	0.53 - 0.73	Galvanised	Galvanized	229	9	499	1,100
ZCS7688	17.8 - 21.6	0.70 - 0.85	Galvanised	Galvanized	229	9	861	1,900
ZCS7689	20.8 - 25.4	0.82 - 1.00	Galvanised	Galvanized	229	9	861	1,900
ZCS7690	24.4 - 31.7	0.96 - 1.25	Galvanised	Galvanized	178	7	861	1,900
ZCS09733	5.6 - 8.1	0.22 - 0.32	304 Stainless Steel	304 Stainless Steel	229	9	294	650
ZCS09734	7.6 - 10.9	0.30 - 0.43	304 Stainless Steel	304 Stainless Steel	229	9	499	1,100
ZCS09735	10.4 - 14.2	0.41 - 0.56	304 Stainless Steel	304 Stainless Steel	229	9	499	1,100
ZCS09736	13.5 - 18.5	0.53 - 0.73	304 Stainless Steel	304 Stainless Steel	229	9	499	1,100
ZCS09737	17.8 - 21.6	0.70 - 0.85	304 Stainless Steel	304 Stainless Steel	229	9	861	1,900
ZCS09738	20.8 - 25.4	0.82 - 1.00	304 Stainless Steel	304 Stainless Steel	229	9	861	1,900
ZCS09739	24.4 - 31.7	0.96 - 1.25	304 Stainless Steel	304 Stainless Steel	178	7	861	1,900

Dimensions

The figures shown are indicative only. Fully dimensioned data-sheets are available on request. Nominal figures/actuals are as per data-sheet with tolerances of +/- 10%. Please contact us if you have any questions.

Range dimension overlaps

If the cable, rope or hose you have lies where ranges overlap, e.g. 1" when sizing is 0.5-1.00 and 1.00-1.5 we recommend that you select your cable grip to achieve break load first. If tensile strengths are equal or both adequate, choose the smaller of the two. Please contact us if you have any questions.

This information is for marketing purposes only. The details contained herein is presented as general information and no representation or warranty is expressly or impliedly given as to its accuracy, completeness or correctness. It does not constitute part of a legal offer or contract. For technical specifications, please contact Slingco Limited.



GET IN TOUCH

☎ 01706 855 558

✉ sales@slingco.com

Slingco Ltd, Gateway Business Park, New Hall Hey Road, Rawtenstall, BB4 6JG t: 01706 855558
Slingco America Inc, 3100 Jonquil Drive SE, Smyrna, Georgia, 30080, USA t: 888 685 9478